

CZ 420 / 485 / 540 / 600 montajes MK-ME-MA-MC001		Carmen Polonio		CZ-420-485-540-600-MK-ME-MA-MC001.dwg	
Drawn by:	Revised by:	Approved by:	Date:	Last modification:	Scale:
Eva Mª Albarracín		19/06/2009	19/06/2009	19/06/2009	1/50
File name:		Technical brochure version:		Version:	
CZ-420-485-540-600-MK-ME-MA-MC001.dwg		4700 A		0	
				Page:	
				1/1	

- ①

Línea de líquido / Ligne de liquide / Liquid line
- ②

Línea de gas / Ligne de Gaz / Gas line
- ③

Evacuación de condensados, entronque M1 1/4" / Evacuation des condensats, tube M1 1/4" / Condensates draining, diameter M1 1/4"
- ④

Entrada agua opcional batería apoyo / Entrée d'eau batterie d'appoint option / Water inlet of optional hot water coil
- ⑤

Salida agua opcional batería apoyo / Sortie d'eau batterie d'appoint option / Water outlet of optional hot water coil
- ⚡

Acometida eléctrica / Alimentation électrique / Power supply
- ↺

Circulación aire interior / Circulation d'air intérieur / Internal air flow
- ↺

Perfil embocaduras: 25 mm / Profil embouchures: 25 mm / Profile outlets: 25 mm

