







Drawn by: Mª Angeles Espejo		Revised by: Carmen Polonio	Approved by: Eva Mª Albarracln	Date: 13/01/2009	Last modification: 13/01/2009	Scale: 1/50
CZ 420-485-540-600 MONTAJE M0020						
File name: CZ-420-485-540-600-M0020.dwg		Technical brochure version: 4700 A		Version: 0	Page: 1/1	



- ①

Línea de líquido / Ligne de liquide / Liquid line
- ②

Línea de gas / Ligne de Gaz / Gas line
- ③

Evacuación de condensados, entronque M1 1/4" / Evacuation des condensats, tube M1 1/4" / Condensates draining, diameter M1 1/4"
- ④

Entrada agua opcional batería apoyo / Entrée d'eau batterie d'appoint option / Water inlet of optional hot water coil
- ⑤

Salida agua opcional batería apoyo / Sortie d'eau batterie d'appoint option / Water outlet of optional hot water coil
- ⚡

Acometida eléctrica / Alimentation électrique / Power supply
- ↶

Circulación aire interior / Circulation d'air intérieur / Internal air flow
- ↶

Perfil embocaduras: 25 mm / Profil embouchures: 25 mm / Profile outlets: 25 mm